

Gasmeter™ CX-4015



Multicomponent FTIR Gas Analyzer

GASMET ON-LINE SERIES includes multicomponent gas analyzers for continuous monitoring applications. The GASMET Cx-4015 incorporates a Fourier Transform Infrared spectrometer, a temperature controlled sample cell, and signal processing electronics. The analyzer is fully equipped for fixed installations and it offers versatility and high performance for all industrial users.

The GASMET Cx-4015 is designed workplace air monitoring, and quality control applications. It is an ideal tool to measure components of interest in ambient conditions. The sample cell can be heated up to 50 °C. Sample cell absorption path length is selected according to the application.

The GASMET Cx-4015 allows simple calibration using only single component calibration gases. The user can easily configure the analyzer for a new set of compounds.

General parameters

Measuring principle:	Fourier Transform Infrared, FTIR
Performance:	simultaneous analysis of up to 50 gas compounds
Response time, T₉₀:	typically < 120 s, depending on the gas flow and measurement time
Operating temperature:	5 - 30°C non condensing air conditioning recommended
Storage temperature:	-20 - 60°C, non condensing
Power supply:	100-115 or 230 V / 50 -60 Hz
Power consumption:	300 W

Spectrometer

Resolution:	recommended 8 cm ⁻¹ or 4 cm ⁻¹
Scan frequency:	10 scans / s
Detector:	Peltier cooled MCT
Source:	SiC, 1550 K
Beamsplitter:	ZnSe
Window material:	ZnSe
Wavenumber range:	900 - 4 200 cm ⁻¹

Sample Cell

Structure:	Multi-pass, fixed path length 9.8 m
Standard material:	100 % Rhodium coated aluminium
Mirrors:	fixed, protected gold coating
Volume:	0.4 l
Connectors:	Inlet Swagelok 6 mm Outlet Swagelok 8 mm
Gaskets:	Viton® O-rings
Temperature:	50 °C, maximum
Window material:	AR coated ZnSe

Measuring parameters

Zero point calibration:	24 hours, calibration with nitrogen (4.0 or higher N ₂ recommended)
Zero point drift:	< 2 % of measuring range per zero point calibration interval
Sensitivity drift:	none
Linearity deviation:	< 2 % of measuring range
Temperature drifts:	< 2 % of measuring range per 10 K temperature change
Pressure influence:	1 % change of measuring value for 1 % sample pressure change. Ambient pressure changes measured and compensated

Electrical Connectors

Digital Interface:	9-pole D-Connector for RS-232 Analyzer is connected to an external computer via RS-232C cable. The external computer controls the GASMET.
Power connection:	Standard plug CEE-22

Gas Inlet and Outlet Conditions

Gas temperature:	non-condensing, the sample gas temperature should be the same as the sample cell temperature
Flow rate:	120 - 600 l per hour
Gas filtration:	filtration of particulates (2µ) required
Sample gas pressure:	ambient
Sample pump:	external, not included

Electronics

A/D Converter:	dynamic range 95 dB
Signal Processor:	32-bit floating point DSP 120 MFLOPS
Computer:	external, not included

Analysis Software (for external PC)

Operating system:	Windows XP
Analysis software:	CALCMET for Windows

Options

Sample Cell:	Multi-pass, fixed path length 2.5 m or 5.0 m
Pressure measurement:	Inside sample cell
External PC:	GASMET PC for control and analysis with optional alarm relay boards and analog inputs or outputs
Sample cell gaskets:	Teflon® coated Viton® or Kalrez®

Enclosure

Material:	Aluminium
Dimensions (mm):	482 * 196 * 450
Weight:	17 kg
CE - Label:	according to EMI guideline 89/336/EC

